


DACLON NYLON

DACLON
NYLON



Type	Monofilament
Composition	Extrusion of polyamide 6.0 or 6.6
Coating	None
Colour	Black
Tissue reaction	Minimal
Absorption	Non absorbable, gradually encapsulated by connective tissue. The thread mass diminishes, approximately 10% a year by rupture of chemical links (hydrolytic action).
Presentation	Box with 12 sutures

*For quality
&
safety*

smi

www.sutures.be

DACLON

NYLON

CHARACTERISTICS

- ✓ High tensile strength, non absorbable
- ✓ Synthetic
- ✓ Monofilament with microscopic uniform diameter
- ✓ Pliability and softness
- ✓ Hermetically sealed packing

BENEFITS

- Excellent and permanent tissue support
- Minimal tissue reaction
- Soft passage through the tissues without sawing, tissue drag and trauma
- Absence of capillarity (no support of bacterial growth)
- Excellent knot tie down
- Good handling properties
- Easy and secure knotting
- Guaranteed seal and product sterility

INDICATIONS General soft tissue closing
and/or ligation
especially in Plastic surgery
Ophthalmic surgery

 Round bodied taper point double armed	Metric	USP	Length	Order number
---	--------	-----	--------	--------------

1/4 circle



2 x VR 8 mm
220 µm



Metric	USP	Length	Order number
0.4	8/0	45 cm	<i>black</i> ON81

 Side cutting spatula	Metric	USP	Length	Order number
--	--------	-----	--------	--------------

1/2 circle



HSP 5.5 mm
150 µm



Metric	USP	Length	Order number
0.2	10/0	30 cm	<i>black</i> ON1081

 Side cutting spatula double armed	Metric	USP	Length	Order number
---	--------	-----	--------	--------------

1/2 circle



2 x HSP 5.5 mm
150 µm



2 x HSP 6.2 mm
150 µm



2 x HSP 6.4 mm
220 µm



2 x HSP 8 mm
300 µm



Metric	USP	Length	Order number
0.2	10/0	30 cm	<i>black</i> ON108
0.2	10/0	30 cm	<i>black</i> ON102
0.2	10/0	30 cm	<i>black</i> ON106
0.7	6/0	45 cm	<i>black</i> ON62

 Side cutting spatula	Metric	USP	Length	Order number
--	--------	-----	--------	--------------








3/8 circle









DSP 6.2 mm
150 µm



Metric	USP	Length	Order number
0.2	10/0	15 cm	<i>black</i> ON1011

 Side cutting spatula double armed	Metric	USP	Length	Order number			
	2 x DSP 6 mm 220 µm		0.2	10/0	30 cm	<i>black</i>	ON103
			0.1	11/0	20 cm	<i>black</i>	ON111
			0.2	10/0	30 cm	<i>black</i>	ON101
	2 x DSP 6.2 mm 150 µm		0.3	9/0	30 cm	<i>black</i>	ON95
			0.3	9/0	45 cm	<i>black</i>	ON95-45
			0.4	8/0	30 cm	<i>black</i>	ON85
			0.4	8/0	45 cm	<i>black</i>	ON85-45
	2 x DSP 6.2 mm 200 µm		0.5	7/0	30 cm	<i>black</i>	ON75
	2 x DSP 6.4 mm 220 µm		0.2	10/0	30 cm	<i>black</i>	ON105
			0.2	10/0	38 cm	<i>black</i>	ON105-38
		0.2	10/0	45 cm	<i>black</i>	ON105-45	
2 x DSP 8 mm 300 µm		0.7	6/0	45 cm	<i>black</i>	ON61	

 Side cutting spatula double armed	Metric	USP	Length	Order number			
	2 x VSP 8 mm 350 µm		1	5/0	45 cm	<i>black</i>	ON51

 Reverse cutting	Metric	USP	Length	Order number			
	DS 12 mm		0.5	7/0	75 cm	<i>black</i>	9051512
			0.7	6/0	75 cm	<i>black</i>	9071512